





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NO. | PANEL DIMENSIONS |            | WEIGHT     |         |
|------------------|------------------|------------|------------|---------|
|                  | THICKNESS        | HOLE SIZE  | lbs (g)    | 100 pcs |
| BEC3P75H25-___   | 0.118 MAX (3.0)  | 0.25 (6.4) | 1.05 (475) |         |

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.



DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS G03415BA\_DC\_GB0239MG/01A

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

BEVELED ENTRY CLIP WITH INTEGRAL PUSH BARB (BEC3P75H25)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE  
PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE FULL

DATE 5/22/06

NYLON 6/6

DRAWING NO.  
GB0239MG

DWG  
A  
SIZE

|     |          |      |     |                                    |          |     |      |     |  |
|-----|----------|------|-----|------------------------------------|----------|-----|------|-----|--|
| 01A | 8-26-08  | TMSA |     | REVISED GEOMETRY ADDED LOGO TO TOP | GB0239MG | 01A |      |     |  |
| R   | 10-18-06 | JAD  |     | INITIAL RELEASE                    | GB0239MG | R   |      |     |  |
| REV | DATE     | BY   | CHK | DESCRIPTION                        | ECN      | - R | CUST | SUP |  |