

REV. BN

NOTES:

1. MINIMUM CONTACT RETENTION: 0.5 LB PER PIN.
2. -01 POSITION OFFERED FOR SINGLE ROW RIGHT ANGLE ONLY.
3. -01, -02 & -03 POSITIONS TO BE LAYER PACKAGED.
4. STOCK TO BE 62 POSITION FOR -D AND 61 POSITION FOR -S, -01 LEAD STYLE ONLY. TO BE CUT TO POSITION FOR CUSTOMER.
5. .005 [.13] MAX SHEAR BURR ALLOWANCE.


DO NOT SCALE
FROM THIS PRINT

FIG. 1




FIG. 2
POLARIZATION OPTION LOCATION
INSERT PK-07 INTO SPECIFIED
POSITION AND BREAK OFF TAB

TABLE 2			
ROW SPEC.	NO. OF POS.	PKG TUBE	TUBE PLUG
-03-S	04-50	PT-1-24-06-17	TP-24
-02-S	05-50	PT-1-24-10-03	TP-03
-01-S-RA	04-50	PT-1-24-01-43	TP-24
-01-D	04-50	PT-1-24-02-17	TP-09
-02-D	04-50	PT-1-24-01-34	TP-07
-03-D	04-50	PT-1-24-01-22	TP-03
-01-D-RA	04-50	PT-1-24-01-45	TP-03
-01-T	04-50	PT-1-24-05-09	TP-07
-02-T	04-50	PT-1-24-01-102	TP-07
-03-T	04-50	PT-1-24-08-15	TP-07
-01-Q	04-50	PT-1-24-15-29	TP-07
-02-Q	04-50	PT-1-24-02-51	TP-13
-03-Q	04-50	PT-1-24-16-29	TP-07
-01-T-RA	04-50	PT-1-24-06-40	TP-07
-01-S	04-50	PT-1-24-05-15	TP-24
ALL STYLES	-02 & -03	LAYER PACKAGING	

TABLE 1		
LEAD STYLE	'A'	CONTACT
-01	.090 [2.29]	C-79-01-X
-01-S-RA	N/A	C-79-53-X
-01-D-RA	N/A	C-79-12-X
-01-T-RA	N/A	C-79-53-X
-01-Q-RA	N/A	C-79-12-X
-02	.600 [15.24]	C-79-02-X
-03	.208 [5.28]	C-79-53-X

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

(THIS VIEW DRAWN TO SHOW HOW PLUG IS ORIENTED IN TUBE FOR THE -02-D STYLE)

MATERIAL:
CONTACT: PHOS BRONZE
INSULATOR: LCP
COLOR: BLACK
MAX BOW: .004 IN/IN

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: BRATCHER 7-24-95

SQT-1XX-XX-XXX-X-XXX-XXX
SHEET 1 OF 3