




Specification:

Material:

Insulator: PBT, rated UL94V-0

Contacts: Brass

Shell: Steel

Contact Plating:

Gold Flash/Nickel

Electrical:

Operation Voltage: 250 VAC max.

Current Rating: 3 Amps max

Contact Resistance: 15 mohms max

Insulation Resistance: 3000 mohms min @ 500 VDC

Dielectric Withstanding Voltage: 1000 Vac/minute

Operating Temperature: -55°C to +105°C

Description	
Name :	
A-DF09LL-TL-B-R	
D-Sub Solder (Female)	
ASSMANN Electronic Components	



THIS DRAWING IS UNPUBLISHED

©Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.