




TAPE MTG DETAIL
SCALE 2:1

- 1

0.76μm [.000030] MIN GOLD OVER 1.27μm [.000050] MIN NICKEL.
2.

PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 0.64 [.025] DIA SPHERE.
- 3

WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:

1.

FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-

A.

1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX

2.

FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-

A.

1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL

B.

5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL

4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4	OBSOLETE	SMALL PACK	202507-3
4	OBSOLETE	TAPE MTG (SEE DETAIL) 3	202507-2
		STANDARD	202507-1
PACKAGING TYPE			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 04/07/93	TE TE Connectivity	
DIMENSIONS: MM[INCHES]		CHK R.STONE 4-26-93		
		APVD R.S.KLINE 4-29-93	NAME	
			PRODUCT SPEC	
			APPLICATION SPEC	
			FINISH	
MATERIAL		WEIGHT	SIZE	
PIN BODY: COPPER ALLOY			A2	
SPRING: STAINLESS STEEL			CAGE CODE	
			00779	
			DRAWING NO	
			G-202507	
			RESTRICTED TO	
			-	
			SCALE	
			10:1	
			SHEET	
			1 of 1	
			REV	
			F2	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

1471-9 (3/11)