

HBL7485V -- Twist-Lock Valise Plug




3P3W, 15A 125/250V, ML-3P, Black Nylon Body

Product Specifications

Product Type	 Twist-Lock Devices	
Product Item	Plug	
Wiring Scheme	3 Pole, 3 Wire Non-Grounding	
Amperage	15A	
Voltage	125/250V AC	
NEMA Configuration	ML-3P	
Item Style	Valise	
Device Color	Black	
Cord Dia.	.300"-.430" (7.6-10.9)	
Blade Holder Material	Black Nylon	
Housing Material	Black nylon	
Cord Clamp Material	Nylon	
Blade Material	Brass	
Terminal Clamp Material	Cold rolled steel-nickel-plated	

Cord Clamp Screw Material	Steel zinc plated
Body Holding Screw Material	Steel zinc plated
Ratings	Molded into face
Dielectric Voltage Withstand	2,000 minimum
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A-#14AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, White)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	UL
Catalog Page	Click here for catalog page B34
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358523743
Weight in LBs	0.1



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

