





CIRCUIT: SPDT

CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
ON	NONE	ON
2-3	OPEN	2-1



RECOMMEND MOUNTING LAYOUT



COPLANAR WITHIN 0.10 [.004] TOTAL.

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. CONTACT RATING: 1 AMP @250VAC;
3 AMP@120 VAC OR 28VDC
5. FIXED TERMINAL & MOVING CONTACT: SILVER PLATED COPPER
6. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLE
AT FULL LOAD.
7. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
8. OPERATING TEMP.: -30°C to 85°C
- ▲ 9. PACKAGING: TAPE AND REEL
10. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®

A	14173	RELEASED FOR PRODUCTION	7/19/04	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE

200BWMSP1T2A1SM6QE

SCALE

2:1

DATE

7/19/04

DR

AR

DWG

T833041

REV

A