

[illegible]

WEIGHT (g)	C	B	A	Pos.	P/N	
					BLUE	GRAY
0.97	31.5	30.5	28.5	20	7-292271-0	2-292271-0
0.92	30.0	29.0	27.0	19	6-292271-9	1-292271-9
0.87	28.5	27.5	25.5	18	6-292271-8	1-292271-8
0.83	27.0	26.0	24.0	17	6-292271-7	1-292271-7
0.78	25.5	24.5	22.5	16	6-292271-6	1-292271-6
0.73	24.0	23.0	21.0	15	6-292271-5	1-292271-5
0.68	22.5	21.5	19.5	14	6-292271-4	1-292271-4
0.64	21.0	20.0	18.0	13	6-292271-3	1-292271-3
0.59	19.5	18.5	16.5	12	6-292271-2	1-292271-2
0.54	18.0	17.0	15.0	11	6-292271-1	1-292271-1
0.49	16.5	15.5	13.5	10	6-292271-0	1-292271-0
0.45	15.0	14.0	12.0	9	5-292271-9	292271-9
0.40	13.5	12.5	10.5	8	5-292271-8	292271-8
0.35	12.0	11.0	9.0	7	5-292271-7	292271-7
0.30	10.5	9.5	7.5	6	5-292271-6	292271-6
0.26	9.0	8.0	6.0	5	5-292271-5	292271-5
0.21	7.5	6.5	4.5	4	5-292271-4	292271-4
0.16	6.0	5.0	3.0	3	5-292271-3	292271-3
0.11	4.5	3.5	1.5	2	5-292271-2	292271-2

DIMENSIONS:		DWN		MATERIAL		FINISH	
mm		-		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK		TE Connectivity			
0 PLC ±		APVD		NAME			
1 PLC ±0.1		-		MT REC ASSY (GOLD-PL.)			
2 PLC ±0.01		-		FOR AMP MINI CT 1.5mm PITCH CONN.			
3 PLC ±0.001		PRODUCT SPEC		SIZE			
4 PLC ±0.0001		APPLICATION SPEC		CAGE CODE		DRAWING NO	
ANGLES ±		-		A4 00779		C=292271	
WEIGHT		-		SCALE			
CUSTOMER DRAWING		-		NON		SHEET 2 OF 2	
		-		REV		B1	