



LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD		
	B	REVISED PER ECO 13-001843.			08FEB2013	MGM	CT		


D







SINGLE POLARIZATION



DOUBLE POLARIZATION



THREE KEY POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

1 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT ID.

2. DWV RATING: 875VAC @ SEA LEVEL

3. WIRE SIZE: 24 AWG MAX

4. WORKING TEMPERATURE: -55°C ~ +125°C

5 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK

6 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

7 ALL TOLERANCES ±0.20MM UNLESS NOTED.

CHROMIUM-BLACK	THREE	SOLDERING	10	11	33.35	ϕ12.5	ϕ15.5	3	2221612-3
CHROMIUM-BLACK	DOUBLE	SOLDERING	10	11	33.35	ϕ12.5	ϕ15.5	3	2221612-2
CHROMIUM-BLACK	SINGLE	SOLDERING	10	11	33.35	ϕ12.5	ϕ15.5	3	2221612-1
FINISH	POLARIZATION	TERMINATION	Q	S	L	d	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	4DEC2012	TE Connectivity			
			CHK	MANJUNATH				
			R.	GROSS				
			APVD	R.				
			PRODUCT SPEC			NAME		
			108-127005			CIRCULAR HD PLUG WITH PIN CONTACTS		
			APPLICATION SPEC			10 POS.		
						-		
			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
			A2	00779	C=2221612	-		
			CUSTOMER DRAWING			SCALE	SHEET	REV
						NTS	1 of 1	B