


# PIN RECEPTACLES

FOR 0,56 - 0,81 DIAMETER PINS

## 0295

0295-0-15-XX-06-XX-10-0


Solder mount in 1,60 min. mounting hole  
Also available on 24mm wide carrier tape:  
1,000 parts per 330mm reel  
Order as: 0295-0-57-XX-06-XX-10-0



## 0292

0292-0-15-XX-06-XX-10-0


Solder mount in 1,8 min. mounting hole



## 0294

0294-0-15-XX-06-XX-10-0


Solder mount in 1,93 min. mounting hole



## 0398

0398-0-15-XX-06-XX-04-0


Press-fit in 1,68 mounting hole



## 0397

0397-X-15-XX-06-XX-04-0

Press-fit in 1,68 mounting hole




| Basic Part Number | Length V |
|-------------------|----------|
| 0397-0            | 8,97     |
| 0397-1            | 8,46     |
| 0397-2            | 10,49    |

## 0297

0297-0-15-XX-06-XX-04-0


Press-fit in 1,7 mounting hole



## 9019/9039

90X9-0-19-XX-06-XX-10-0

Press-fit in 1,91 mounting hole



| Basic Part Number | Head Dia. C |
|-------------------|-------------|
| 9019-0            | 3,18        |
| 9039-0            | 2,54        |

### SPECIFICATIONS:

**Shell Material:** Brass Alloy 360, 1/2 Hard

**Contact Material:** Beryllium Copper Alloy 172, HT

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$

Diameters:  $\pm 0,051$

Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 06 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#06 CONTACT (DATA ON PAGE 255)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com