



main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes

crocodile clips

- ▶ 0,64 mm system
- ▶ 2 mm system
- ▶ 4 mm system
- ▶ 4 mm safety system

test probes

oscilloscope test probes

measuring leads

plugs

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ crocodile clips ▶ crocodile clips ▶ MA 260 SH


MA 260 SH

datasheet for MA 260 SH
 article number: 973889101



View Full-Size Image



product description:	Bestellnummer: 973 889-101
description:	Contact-protected Miniature alligator clip with high strength insulation and nickel-plated bronze jaws. Clamping range up to a bolt diameter of 6 mm. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. 4 mm diameter brass socket connection.
typ:	MA 260 SH rot/red
system:	4 mm safety system
order number:	973 889-101
clamping range:	6 mm
color versions:	
technical data	
type of contact:	clamp
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 300 V
rated current:	15 A
contact resistance:	10 mOhm
material	
contact material:	bronze
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-25 °C to +80 °C
flammable class:	
housing:	UL 94 HB
drawing	

search online catalogue

Search

Search

Messetermine

No events

QR-Code

