

9035 Monochrome Laser Printer

Unmatched Fusion of Performance and Productivity.



- Less than 9 seconds first page output time
- 1200 x 1200 dpi at up to 35 ppm
- Powerful 405 MHz RISC processor
- Intellifilter for compatibility with legacy print data streams
- Intelliprint controller
- Adobe PostScript 3, PCL6, PCL5e
- Optional duplex printing
- Duty cycle of 150,000 images per month
- One year on-site warranty

Excellent Speed, Robust Duty Cycle.

The 9035 prints at speeds up to 35 pages per minute with a first page out time of less than 9 seconds. In addition to the rapid printing speeds, the 9035 is capable of handling duty cycles of up to 150,000 pages per month. This kind of performance allows the 9035 to be relied upon in even the most demanding printing environments.

Productivity Enhancing Controller Architecture.

The 9035 incorporates the Intelliprint controller architecture – a proprietary printing control technology developed by TallyGenicom to provide users with an unmatched fusion of performance and productivity enhancement. Features such as password-protected printing, saved job library and job accounting set the 9035 apart from the competition.

Intelliprint controller architecture

In addition to the productivity enhancements offered by the Intelliprint controller architecture, the 9035 also boasts a class-leading 405 MHz processor, Adobe PostScript 3 and PCL6 and PCL5e functionality.

Available Configuration:

9035N - Ethernet, Parallel, USB, PS3

9035ND - Ethernet, Parallel, USB, PS3, with duplexer

9035NDT - Ethernet, Parallel, USB, PS3, with duplexer and extra tray

9035M - MICR, Ethernet, Parallel, USB, PS3

9035ME - MICR-extended security laser printer, e-net, PS3

Print Speed	35 ppm
Print Method	Electro-photographic semiconductor laser with Intelliprint Controller
Processor	MIPS R5000 405 MHz
Resolution	1200 x 1200 dpi
Time To 1st Page	Less than 9 Seconds
Memory	64MB expandable to 320MB (2 slots); Optional 20GB (or higher) hard disk
Standard Connectivity	10/100Base-T Ethernet; TCP/IP, EtherTalk, Bonjour; IEEE 1284 parallel; Hi-Speed USB 2.0 480 Mb/s auto interface switching
Standard Emulation	PostScript 3; PCL6 with PjL, PCL5e
Print Monitor	SNMP, Printer MIB, e-mail status, and Web-based status and control, TGNetAdmin
Fonts	136 Adobe PostScript fonts; 86 Type 1 PCL
Consumables	Single element toner cartridge with 17,000 pages (at 5%). New printer comes with 10,000 letter/A4 yield capacity.
Maintenance	200K Letter/A4
STD Paper Handling	550-sheet tray; 150-sheet tray
Opt'l Paper Handling	550-sheet feeder tray (up to 2 additional)
Duplexing	Optional
Paper Type	Sheet paper, transparencies, bond, labels, envelopes, and thick media
Paper Weight	16 to 58 lbs (60 to 216 g/m ²) in simplex and duplex modes
Paper Size	Letter, executive, legal, folio, A4, A5, A6, B5, statement; Envelopes: Com10, Monarch, DL, C5; Custom sizes: 3.88 to 8.50 W by 5.83 to 14.00 L (tray 1 and 2 only); Officio (8.5" x 13.38" - supported as a custom size in tray #1 or #2)
Paper Output	500-sheet face-down top output; Optional cassette: 500-sheet offset catch tray
Physical Weight	45 lbs. (20.6 kg)
PhysicalSize	15.9" x 16.6" x 18.3" (404x 422 x 465 mm)
Power Voltage	100/120-127 VAC, 50/60 Hz; Current: 7 amps
Power Consumption	5.38 kWh/Week or less for ENERGY STAR® qualified models
Compliance	ENERGY STAR® qualified, Ozone-free; UL950, FCC part 15 Class B, ICES 003, CISPR22 Class B, FDA CDRH, cUL, CE, GS, IEC 825,GOST (Russia), SABS (S. Africa), C-Tick (Australia), RoHS, Microsoft, ISO-compliant, Meditech Approved
Workload	Up to 150,000 pages per month
Forms Software	Intellifilter; Optional: Intellipress
Drivers	Vista, XP, 2003, 95, 98, 2000, Me, NT 4.0; Mac OSX, Adobe PostScript and PCL drivers included; Unix and Linux compatibility
Temperature	Operating: 41° F - 95° F (5° to 35° C)
Humidity	Operating: 15%-85% Non-Condensing
Acoustic	Printing - 53.6 dB(A); Standby - 27 dB(A)
Warranty	One year on-site
Option 1	Add-on tray - 550 sheet feeder; duplexer; offset catch tray
Option 2	128MB DIMM; 256MB DIMM
Option 3	Intelliprint Barcode Module; Intelliprint Barcode/Real Time Clock Module; Intelliprint Real Time Clock
Options 4	Hard disk
Option 5	RS232 interface
Note	Exceeding the monthly duty cycle will not void the warranty if TallyGenicom consumables and maintenance kits are used. Toner saver mode provides up to 40% savings.



© 2009 Printronix, Inc. All rights reserved. Genicom, Tally, TallyGenicom, TG TallyGenicom, the TG Logo, Intellifilter, Intelliprint and Intellipress are trademarks or registered trademarks of Printronix, Inc. Microsoft, Windows, and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. All other trademarks, product names, company names or logos herein are the property of their respective owners. Product appearance and/or specifications are subject to change without notice.

Printed Date: 16/05/2009

PRINTRONIX®

GLOBAL PRINTING...ENABLED.

14600 Myford Road
Irvine, CA 92606
800-665-6210
www.tallygenicom.com