


[Printer Friendly](#)

[HOME](#) | [SOLUTIONS](#) | [RESOURCE](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)

SEARCH



Current refinements (click to remove)

[Search Tips](#)

☐ Region USA ☐ Product Family Adhesive Lined Grommet Edging Polyethylene Solid Wall

Text Search: 'GES144FA-C'

Your search criteria matched only one product, shown below.

Related Products

[Click here to see Image](#)

Protects and insulates wires and cables from chafing against edges

[Slotted Wall](#)

[Flame Retardant Grommet Edging R...](#)

[Grommet Edging Nylon – Slotte...](#)

[Grommet Edging Polyethylene –...](#)

[Grommet Edging](#)

- General purpose material for indoor use up to 122°F (50°C)
- Provided in .030" (0.8mm) thick material making it highly flexible
- Use on straight edges
- Adhesive ensures product stays in place

‡Reel packaging may contain splices.

* Order the number of reels required.

Part Number: GES144FA-C

RoHS Compliancy Status Compliant

Part Description: Solid Wall Polyethylene Grommet Edging with adhesive edge. This product will stay where it is installed on straight edges.

Product Type: Grommet Edging

Material: Polyethylene

Color: Natural

Height (In.): .22

Height (mm): 5.6

Length (ft.): 100

Length (m): 30.5

Width (In.): .21

Width (mm): 5.3

Flammability Rating: UL HB

Ft. Per Pkg.: 100

Outside Depth (In.): .222

Outside Depth (mm): 5.6

Outside Width (In.): .213

Outside Width (mm): 5.4

Panel Thickness Range (In.): .099– .144

Panel Thickness Range (mm): 2.5– 3.7

Temperature Range: -40°F to 122°F (-40°C to 50°C)

Min. Order UOM: RL

Min. Order Qty.: 1

BOM Qty. (# of Pkgs.)

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[View Content Details](#)

[Evaluate](#)

[Design a Solution](#)

[Install & Maintain](#)

Product Bulletins:

☐ [Adhesive Lined Grommet Edging Sa101n...](#)