

## 2035 Screwdriver for slotted screws



**Application:** Slotted screws  
**Blade:** Round, mat nickel  
**Tip:** DIN 8320 up to 0,3 x 1,8;  
 DIN 5264-A/ISO 2380 as of 0,4 x 2,0, Black Point  
**Handle:** Kraftform Micro® with anti-roll protection and rotating cap, multi component

| Code        | mm   | mm  | mm  | mm | mm  | mm    | mm      | mm | mm |
|-------------|------|-----|-----|----|-----|-------|---------|----|----|
| 05117990001 | 0,16 | 0,8 | 40  | 97 | 2,0 | 1/32" | 1 9/16" | 10 |    |
| 05117991001 | 0,18 | 1,0 | 40  | 97 | 2,0 | 0,04" | 1 9/16" | 10 |    |
| 05117992001 | 0,20 | 1,2 | 40  | 97 | 2,0 | 0,05" | 1 9/16" | 10 |    |
| 05118000001 | 0,25 | 1,2 | 40  | 97 | 2,0 | 0,05" | 1 9/16" | 10 |    |
| 05118001001 | 0,25 | 1,2 | 60  | 97 | 2,0 | 0,05" | 2 3/8"  | 10 |    |
| 05118002001 | 0,23 | 1,5 | 40  | 97 | 2,0 | 1/16" | 1 9/16" | 10 |    |
| 05118003001 | 0,23 | 1,5 | 60  | 97 | 2,0 | 1/16" | 2 3/8"  | 10 |    |
| 05117993001 | 0,30 | 1,8 | 40  | 97 | 2,0 | 0,07" | 1 9/16" | 10 |    |
| 05118004001 | 0,30 | 1,8 | 60  | 97 | 2,0 | 0,07" | 2 3/8"  | 10 |    |
| 05118005001 | 0,40 | 2,0 | 40  | 97 | 2,5 | 5/64" | 1 9/16" | 10 |    |
| 05118006001 | 0,40 | 2,0 | 60  | 97 | 2,5 | 5/64" | 2 3/8"  | 10 |    |
| 05118007001 | 0,40 | 2,0 | 100 | 97 | 2,5 | 5/64" | 4"      | 10 |    |
| 05117994001 | 0,40 | 2,5 | 50  | 97 | 2,5 | 5/64" | 2"      | 10 |    |
| 05118008001 | 0,40 | 2,5 | 80  | 97 | 2,5 | 3/32" | 3 1/8"  | 10 |    |
| 05118009001 | 0,40 | 2,5 | 100 | 97 | 2,5 | 5/64" | 4"      | 10 |    |
| 05117995001 | 0,50 | 3,0 | 50  | 97 | 3,0 | 1/8"  | 2"      | 10 |    |
| 05118010001 | 0,50 | 3,0 | 80  | 97 | 3,0 | 1/8"  | 3 1/8"  | 10 |    |
| 05118011001 | 0,50 | 3,0 | 100 | 97 | 3,0 | 1/8"  | 4"      | 10 |    |
| 05117996001 | 0,50 | 3,0 | 150 | 97 | 4,0 | 5/32" | 4"      | 10 |    |
| 05118012001 | 0,60 | 3,5 | 80  | 97 | 4,0 | 9/64" | 3 1/8"  | 10 |    |
| 05118014001 | 0,80 | 4,0 | 80  | 97 | 4,0 | 5/32" | 3 1/8"  | 10 |    |
| 05118015001 | 0,80 | 4,0 | 100 | 97 | 4,0 | 5/32" | 4"      | 10 |    |
| 05118016001 | 0,80 | 4,0 | 150 | 97 | 4,0 | 5/32" | 6"      | 10 |    |

## 2050 PH Screwdriver for Phillips screws



**Application:** Phillips-Recess  
**Blade:** Round, mat nickel  
**Drive tip:** DIN 5260-PH, ISO 8764-PH; Black Point  
**Handle:** Kraftform Micro® with anti-roll protection and rotating cap, multi component

| Code        | mm    | mm  | mm | mm  | mm      | mm | mm | mm |
|-------------|-------|-----|----|-----|---------|----|----|----|
| 05118019001 | PH 00 | 40  | 97 | 2,5 | 1 9/16" |    |    | 10 |
| 05118020001 | PH 00 | 60  | 97 | 3,0 | 2 3/8"  |    |    | 10 |
| 05118022001 | PH 0  | 60  | 97 | 3,0 | 2 3/8"  |    |    | 10 |
| 05118023001 | PH 1  | 60  | 97 | 4,0 | 2 3/8"  |    |    | 10 |
| 05118024001 | PH 1  | 80  | 97 | 4,0 | 3 1/8"  |    |    | 10 |
| 05118025001 | PH 1  | 100 | 97 | 4,0 | 4"      |    |    | 10 |

## 2055 PZ Pozidriv screwdriver for electronics use



**Application:** Suitable for Pozidriv® screws  
**Blade:** Round, mat nickel  
**Drive tip:** DIN 5260-PZ, ISO 8764-PZ; Black Point  
**Handle:** Kraftform Micro® with anti-roll protection and rotating cap, multi-component

| Code        | mm   | mm | mm | mm  | mm     | mm | mm | mm |
|-------------|------|----|----|-----|--------|----|----|----|
| 05118030001 | PZ 0 | 60 | 97 | 3,0 | 2 3/8" |    |    | 10 |
| 05118032001 | PZ 1 | 80 | 97 | 4,0 | 3 1/8" |    |    | 10 |

\*) Pozidriv = reg. trademark of European Industrial Service Ltd.

## 2067 TORX® screwdriver for electronics use



**Application:** TORX® socket screws  
**Blade:** Round, mat nickel  
**Drive tip:** TORX®, Black Point  
**Handle:** Kraftform Micro® with anti-roll protection and rotating cap, multi-component

| Code        | mm   | mm | mm | mm  | mm      | mm | mm | mm |
|-------------|------|----|----|-----|---------|----|----|----|
| 05118035001 | TX 1 | 40 | 97 | 2,0 | 1 9/16" |    |    | 5  |
| 05118036001 | TX 2 | 40 | 97 | 2,0 | 1 9/16" |    |    | 5  |
| 05118037001 | TX 3 | 40 | 97 | 2,0 | 1 9/16" |    |    | 5  |
| 05118039001 | TX 4 | 40 | 97 | 2,5 | 1 9/16" |    |    | 5  |
| 05118040001 | TX 5 | 40 | 97 | 3,0 | 1 9/16" |    |    | 5  |
| 05118042001 | TX 6 | 40 | 97 | 3,0 | 1 9/16" |    |    | 5  |

## 2052 Ballhead Hexagon Screwdriver



**Application:** Ball-head design for hex socket screws  
**Blade:** Round, mat nickel  
**Tip:** Width corresponds to ISO 2936, Black Point  
**Handle:** Kraftform Micro® with anti-roll protection and rotating cap, multi-component

| Code        | mm  | mm    | mm | mm | mm  | mm     | mm | mm |
|-------------|-----|-------|----|----|-----|--------|----|----|
| 05118089001 | 1,3 |       | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118090001 | 1,5 |       | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118092001 | 2,0 |       | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118094001 | 2,5 |       | 60 | 97 | 4,0 | 2 3/8" |    | 5  |
| 05118096001 | 3,0 |       | 60 | 97 | 4,0 | 2 3/8" |    | 5  |
| 05118098001 |     | 1/16" | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118100001 |     | 5/64" | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118102001 |     | 3/32" | 60 | 97 | 3,0 | 2 3/8" |    | 5  |
| 05118106001 |     | 7/64" | 60 | 97 | 4,0 | 2 3/8" |    | 5  |
| 05118103001 |     | 1/8"  | 60 | 97 | 4,0 | 2 3/8" |    | 5  |