








Dimensions: mm (In.)



101-0363-EV



101-0463-EV

**Mechanical Specifications:**

- Mechanical life: 500,000 cycles
- Operating temperature: -25°C to +70°C
- Operating force: 130 ±30g

Electrical Specifications:

- Rating: 50mA/12VDC
- Insulation resistance: >100MΩ min. @ 250VDC
- Dielectric Strength: 250VAC for 1 minute
- Contact resistance: <100mΩ
- Electrical life: 300,000 cycles

Material:

- Contact: phosphor bronze plated silver

Note:

- H: 230" (101-0363-EV), 329" (101-0463-EV)
- RoHS Compliant

Tactile Switches (Thru-Hole)
101-0363-EV, 101-0463-EV

**Mountain
Switch**