

5

4

3

2

1

F


E

D




C

B

A



MOUNTING HOLE DETAIL
(SCALE 1:1)



GENERAL TOLERANCES

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGLE	±3°

	5025-04P1	NO
	5025-04P	YES
EDP NO.	ENG. NO.	MTG. EAR

			公差 (Tolerances)		所要数 (Req)	DRWG. <u>Y. Awano</u> 9/27/77
			.000 → ±0.005 .00 → ±0.05			DSN'D <u>M. EANO/MTO</u> 9/21/77
			.0 → ±0.1 . → ±0.3			CHK'D <u>Ke Shino</u>
			材料 (MAT'L)		★ APP'D	
			NYLON 66, 94V-2			
			熱処理 (H.T.)		molex MOLEX-JAPAN CO., LTD. 日本モレックス株式会社	
			HRc <u> # </u>			
			仕上げ (Finish)			
			<u> # </u>		No.	REV.
					SD-5025-04P*	D
			Scale	名称 (Name)		
			2/1	MINI. FIT CONN. 4POS. PLUG HSG.		
記号 LTR	変更内容 (Rev.)	Date	Name			

D

ADDED -04P1 ECN NO. 917 9/27/77 Y.A.

C

REMOVED "X" ECN NO. 748 9/21/77 M.E.

B

リブ、パネリスロット、サキット NO. 179/77 1/2

A

REVISED 10/28/77 1/2

O

PROPOSED 9/27/77 1/2

記号
LTR

変更内容 (Rev.)

Date

Name

Scale
2/1

名称 (Name)

MINI. FIT CONN. 4POS. PLUG HSG.

所要数
(Req)

molex

MOLEX-JAPAN CO., LTD.
日本モレックス株式会社

No.

SD-5025-04P*

REV.

D

5



4

3

2

1

F





パネル板厚 2mm MAX

パネルスロット寸法
(SCALE 1:1)


E

D



C

B



A

一般公差

10未満	±0.2
10以上30未満	±0.25
30以上	±0.3
角度	±3°

15-31-1043	5025-04P1	無
15-31-1041	5025-04P	有
EDP NO.	ENG. NO.	MTG. EAR

					公差 (Tolerances)	所要数 (Req)	DRWG. <i>Y. Awano</i> 9/27/77	
					.000 → ±0.005 .00 → ±0.05		DSN'D <i>M. ENO</i> 10/10/77	
					.0 → ±0.1 . → ±0.3		CHK'D <i>U. Shiraishi</i>	
					材料 (MAT'L)	* MOLEX-JAPAN CO., LTD. 日本モレックス株式会社	APP'D <i>W. M. S.</i>	
E	REVISED	ECN-NO. 1499	11/30/79	KH	NYLON66, 94V-2		molex	
D	ADDED -04P1 ECN NO. 917	9/5/78			熱処理 (H.T.)			
C	REMOVED "X" ECN NO. 748	3/8/78			HRc — //			
B	リブ、パネルスロット、サキット NO.	12/9/77			仕上げ (Finish)	No.		REV.
A	REVISED	10/28/77			— //	SD-5025-04P*	E	
O	PROPOSED	9/27/77			Scale 2/1	名称 (Name)		
記号 (LTR)	変更内容 (Rev.)		Date	Name	MINI. FIT CONN. 4POS. PLUG HSG.			