


Dimensions: mm (in.)



Electrical Specifications:

- Contact Rating: 0.4VA Max. @ 20V AC or DC Max.
- Contact Resistance: Below 100m Ω typ. initial
- Insulation Resistance: 500M Ω min.
- Dielectric Strength: 500Vrms min.

Mechanical Specifications:

- Life :40,000 make-and-break cycles
- Operating Temperature: -30°C~+85°C

Note:

- RoHS Compliant

Soldering Process:

- Only for Wave Soldering, do not use in IR-Reflow Soldering

Sealed Sub-Miniature Rocker Switch

103-7137-EV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7137-EV](#)