




SCRs

(Continued)

I_T (AMPS)	1.6	4.0			
@ T_C (°C)	55	90	85	85	30
I_{TSM} (AMPS)	6.0	35	30	30	20
    					
	TO-18	TO-39	TO-202	TO-202-2	TO-202
V_{RRM} (VOLTS)					
50	2N6605				
60	2N6606				
100	2N6607				C106A1
200	2N6608	CS39-4B	CS202-4B	CS202-4B-2	C106B1
300					C106C1
400		CS39-4D	CS202-4D	CS202-4D-2	C106D1
500					C106E1
600		CS39-4M	CS202-4M	CS202-4M-2	C106M1
800		CS39-4N			

I_{GT}	200 μ A	200 μ A	200 μ A	200 μ A	200 μ A
V_{GT}	0.8V	0.8V	0.8V	0.8V	0.8V
I_H	5.0mA	5.0mA	5.0mA	5.0mA	5.0mA