



SAFETY DATA SHEET WD40 BULK

According to Regulation (EC) No 1907/2006

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME WD40 BULK

APPLICATION Anti-squeak. Moisture repellent. Releasing agent

SUPPLIER WD40 Company Limited
PO Box 440
Kiln Farm
Milton Keynes
MK11 3LF
Tel: 01908 555400
Fax: 01908 266900
info@wd40.co.uk

EMERGENCY TELEPHONE 00 44 1908 555 400 (08.00 - 16.30)

2 HAZARDS IDENTIFICATION

Flammable. Repeated exposure may cause skin dryness or cracking. Harmful: may cause lung damage if swallowed.

CLASSIFICATION Xn;R65. R10, R66.

PHYSICAL AND CHEMICAL HAZARDS

Flammable.

HUMAN HEALTH

See section 11 for additional information on health hazards. This substance has no evidence of carcinogenic properties.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
PETROLEUM DISTILLATE	265-150-3	64742-48-9	60-80%	Xn;R65. R10,R66.

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

INHALATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Perform artificial respiration if breathing has stopped. Get medical attention immediately!

INGESTION

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Rinse mouth thoroughly. Get medical attention. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Get medical attention immediately!

SKIN CONTACT

Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention promptly if symptoms occur after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Extinguish with foam, carbon dioxide or dry powder.

SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed immediately or cooled with water. Avoid water in straight hose stream; will scatter and spread fire. Keep run-off water out of sewers and water sources. Dike for water control.

PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

WD40 BULK**6 ACCIDENTAL RELEASE MEASURES****PERSONAL PRECAUTIONS**

Wear protective clothing as described in Section 8 of this safety data sheet.

ENVIRONMENTAL PRECAUTIONS

Avoid discharge to the aquatic environment.

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Stop leak if possible without risk. Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

7 HANDLING AND STORAGE**USAGE PRECAUTIONS**

Keep away from heat, sparks and open flame. Avoid inhalation of vapours/spray and contact with skin and eyes.

STORAGE PRECAUTIONS

Keep in original container.

STORAGE CLASS

Flammable liquid storage.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION**HAND PROTECTION**

Rubber gloves are recommended. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Promptly remove any clothing that becomes contaminated. Wash promptly if skin becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid		
COLOUR	Light (or pale) Amber		
ODOUR	Characteristic		
SOLUBILITY	Insoluble in water		
BOILING POINT (°C)	148°C (minimum) 760 mm Hg	RELATIVE DENSITY	0.817 @ 21°C
VAPOUR DENSITY (air=1)	> 1	VOLATILE BY VOL. (%)	57%
FLASH POINT (°C)	44°C TOC (Tag open cup).	FLAMMABILITY LIMIT - LOWER(%)	0.6%
FLAMMABILITY LIMIT - UPPER(%)	8.0%		

10 STABILITY AND REACTIVITY**STABILITY**

Stable under normal temperature conditions and recommended use.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with strong oxidisers.

HAZARDOUS POLYMERISATION

Will not polymerise.

HAZARDOUS DECOMPOSITION PRODUCTS

During fire, toxic gases (CO, CO₂, NO_x) are formed.

11 TOXICOLOGICAL INFORMATION**INGESTION**

Harmful: may cause lung damage if swallowed. May cause discomfort if swallowed. May cause stomach pain or vomiting.

SKIN CONTACT

Repeated exposure may cause skin dryness or cracking.

WD40 BULK

EYE CONTACT

Splashes may irritate.

Other Health Effects

This substance has no evidence of carcinogenic properties.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product is not expected to be hazardous to the environment.

BIOACCUMULATION

The product contains potentially bioaccumulating substances.

DEGRADABILITY

The product is easily biodegradable.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS	3		
PROPER SHIPPING NAME	PETROLEUM DISTILLATES, N.O.S., or PETROLEUM PRODUCTS, N.O.S.		
UN NO. ROAD	1268	UK ROAD PACK GR.	III
ADR CLASS NO.	3	ADR CLASS	Class 3: Flammable liquids.
ADR PACK GROUP	III	HAZARD No. (ADR)	30
ADR LABEL NO.	3	HAZCHEM CODE	3Y
CEPIC TEC(R) NO.	30GF1-III	RID CLASS NO.	3
RID PACK GROUP	III	UN NO. SEA	1268
IMDG CLASS	3	IMDG PACK GR.	III
EMS	F-E, S-E	MARINE POLLUTANT	No.
UN NO. AIR	1268	AIR CLASS	3
AIR PACK GR.	III		

15 REGULATORY INFORMATION

LABELLING



Harmful

CONTAINS PETROLEUM DISTILLATE

RISK PHRASES

R10	Flammable.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.

SAFETY PHRASES

S2	Keep out of the reach of children
S24	Avoid contact with skin.

WD40 BULK

S35	This material and its container must be disposed of in a safe way.
S46	If swallowed, seek medical advice immediately and show this container or label.
S51	Use only in well-ventilated areas.

EU DIRECTIVES

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

STATUTORY INSTRUMENTS

Control of Substances Hazardous to Health.

Chemicals (Hazard Information and Packaging) Regulations.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

CHIP for everyone HSG(108).

Workplace Exposure Limits EH40.

NATIONAL REGULATIONS

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

16 OTHER INFORMATION**REVISION COMMENTS**

Re-issued in accordance with Regulation (EC) No. 1907/2006 Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

REVISION DATE 09-2007

REV. NO./REPL. SDS GENERATED 3 / 02-2007

RISK PHRASES IN FULL

R10	Flammable.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.