


Terminal Blocks

158-P02ESK508V2-E, 158-P02ESK508V3-E



Terminal Blocks

158-P02ESK508V2-E, 158-P02ESK508V3-E



Dimensions: mm (in.)

P	02P	03P
U	5.08	10.16
V	10.16	15.24

MATERIAL SPECIFICATIONS

Solder pin:	Copper, Tin plated
Screw:	Steel, Zinc plated
Wire cage:	Steel, Zinc plated
Housing:	PA66, Green
RoHS Compliant	

ELECTRICAL SPECIFICATIONS

Rating:	300V 23A
Pitch:	5.08 mm
Insulation withstand voltage:	2000V/Min.
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C~+105°C
Screw torque value:	8kgf-cm (Max)
Electric wire:	AWG 26~12

Date Last Revised: 02-03-10

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 301119

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P02ESK508V2-E](#) [158-P02ESK508V3-E](#)