


B45196H, Tantalum, MnO2 Tantalum, 220 uF, 10%, 10 V, SMD, Molded, 6032, Height Max = 2.8mm

**General Information**

Supplier:	KEMET
Series:	B45196H
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, Molded
RoHS:	Yes
Termination:	Tin
Notes:	Obsolete. Old Part Number [Obsolete] Was B45196H2227K306

Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1.8mm TYP

Specifications

Capacitance:	220 uF
Capacitance Tolerance:	10%
Voltage DC:	10 VDC (85C), 6.7 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	12%
Failure Rate:	N/A
Leakage Current:	22 uA

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	8000