

MH5 SERIES

105°C 5mm Height.

◆FEATURES


•RoHS compliance.

◆SPECIFICATIONS

Items	Characteristics																											
Category Temperature Range	-40~+105℃																											
Rated Voltage Range	6.3~50V.DC																											
Capacitance Tolerance	±20% (20℃, 120Hz)																											
Leakage Current(MAX)	I=0.01CV or 3μA whichever is greater. (After 2 minutes application of rated voltage) I=Leakage Current(μA) C=Capacitance(μF) V=Rated Voltage(V)																											
Dissipation Factor(MAX) (tanδ)	<table><tr><td>Rated Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>tanδ</td><td>0.28</td><td>0.24</td><td>0.20</td><td>0.16</td><td>0.13</td><td>0.12</td></tr></table> (20℃, 120Hz)							Rated Voltage (V)	6.3	10	16	25	35	50	tanδ	0.28	0.24	0.20	0.16	0.13	0.12							
Rated Voltage (V)	6.3	10	16	25	35	50																						
tanδ	0.28	0.24	0.20	0.16	0.13	0.12																						
Endurance	After applying rated voltage with rated ripple current for 1000 hours at 105℃, the capacitors shall meet the following requirements. <table><tr><td>Capacitance Change</td><td colspan="6">Within ±25% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td colspan="6">Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td colspan="6">Not more than the specified value.</td></tr></table>							Capacitance Change	Within ±25% of the initial value.						Dissipation Factor	Not more than 200% of the specified value.						Leakage Current	Not more than the specified value.					
Capacitance Change	Within ±25% of the initial value.																											
Dissipation Factor	Not more than 200% of the specified value.																											
Leakage Current	Not more than the specified value.																											
Low Temperature Stability Impedance Ratio(MAX)	<table><tr><td>Rated Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Z(-25℃) / Z(20℃)</td><td>3</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40℃) / Z(20℃)</td><td>8</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr></table> (120Hz)							Rated Voltage (V)	6.3	10	16	25	35	50	Z(-25℃) / Z(20℃)	3	3	2	2	2	2	Z(-40℃) / Z(20℃)	8	5	4	3	3	3
Rated Voltage (V)	6.3	10	16	25	35	50																						
Z(-25℃) / Z(20℃)	3	3	2	2	2	2																						
Z(-40℃) / Z(20℃)	8	5	4	3	3	3																						

◆DIMENSIONS

(mm)



◆MULTIPLIER FOR RIPPLE CURRENT

Frequency (Hz)		60(50)	120	500	1k	10k≤
Coefficient	0.47~1μF	0.50	1.0	1.20	1.30	1.50
	2.2~4.7μF	0.65	1.0	1.20	1.30	1.50
	10~47μF	0.8	1.0	1.20	1.30	1.50
	100μF	0.8	1.0	1.10	1.15	1.20

◆STANDARD SIZE Size φD×L(mm), Ripple Current (mA r.m.s./105°C, 120Hz)

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
6.3 (0J)	22	4×5	23
	33	5×5	30
	47	5×5	37
	100	6.3×5	57
10 (1A)	22	5×5	28
	33	5×5	34
	47	6.3×5	52
	100	6.3×5	62

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
16 (1C)	10	4×5	20
	22	5×5	31
	33	6.3×5	48
	47	6.3×5	56
	100	6.3×5	62
25 (1E)	10	5×5	22
	22	6.3×5	44
	33	6.3×5	48
	47	6.3×5	56

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
35 (1V)	4.7	4×5	17
	10	5×5	24
	22	6.3×5	48
	0.47	4×5	4
50 (1H)	1	4×5	8
	2.2	4×5	13
	3.3	4×5	14
	4.7	5×5	18
	10	6.3×5	28

◆OPTION

	Code
PET Sleeve	EFC

◆PART NUMBER

□□□ MH5 □□□□□ M □□□ □□ D×L
 Rated Voltage Series Capacitance Capacitance Tolerance Option Lead Forming Case Size