



VRLA Rechargeable Battery

BPL65-12



FEATURES

- Maintenance free(no water topping-up required).
- No free acid(Non-spillable battery).
- Low self-discharge rate, lower than 3% capacity loss per month.
- Can be used in any orientation(excluding used inverted).
- Absorbent Glass Mat technology for efficient gas recombination.

APPLICATION

- UPS
- Telecom
- Golf-Carts



SPECIFICATIONS

Nominal Voltage	12 V
Nominal Capacity	65Ah @ 20 hour rate F.V.(1.75V/cell)
Approx. Weight	22.7Kg(50.05lbs.)
Terminals	B5 (Fitting M6 bolt & nut) I2 is optional
Internal Resistance	$\leq 5.0m\Omega$ (Fully Charged)
Max. Discharge Current	650 A (5 sec.)
Max. Charge Current	19.5 A
Operating Temperature Range	Charge : 0°C~40°C(32°F~104°F) Discharge : -20°C~50°C(-4°F~122°F) Storage. : -20°C~40°C(-4°F~104°F)
Container Material	Standard: ABS(UL 94-HB) BPL65-12 Optional: Flame Retardant ABS(UL 94-V0) BPL65-12FR



- IEC 61056-1
- JIS C 8702-1
- GB/T 19639.1

DIMENSION(mm/inch)

OUTER DIMENSIONS

TERMINAL TYPE

Length

350±2.0 (13.78±0.08)

Width



166±2.0 (6.54±0.08)

Container Height

174±2.0 (6.85±0.08)

Total Height

174±2.0 (6.85±0.08)



Terminal Hardware Initial Torque: B5/I2 (5.5Nm±5%)

Constant power discharge characteristics at 25 °C/77 °F

Unit: W

Discharge Time F.V. (V/cell)	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	1568	1298	808	455.0	192.0	132.4	73.90	39.00
1.75V	1700	1362	842	469.0	195.6	134.9	74.70	39.60
1.70V	1769	1408	862	478.0	198.3	136.0	75.20	39.90
1.65V	1833	1442	878	484.0	199.2	136.5	75.50	40.20
1.60V	1878	1465	886	488.0	200.2	136.5	76.00	40.50

Constant current discharge characteristics at 25 °C/77 °F

Unit: A

Discharge Time F.V. (V/cell)	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	141.7	113.8	68.4	40.70	16.39	11.25	6.26	3.30
1.75V	155.7	119.4	71.0	42.30	16.60	11.36	6.35	3.37
1.70V	162.2	123.2	72.7	43.10	16.72	11.53	6.40	3.38
1.65V	166.7	126.7	73.6	43.70	16.78	11.57	6.42	3.39
1.60V	169.2	129.1	74.5	44.20	16.98	11.63	6.42	3.41

All data and artworks shall be changed without prior notice, BB reserves the right to explain and update the information contained hereinto.