



For installation information please refer to the tooling overview and manuals on our website.

Pour les conditions de pose, merci de vous référer à la description de l'outil et aux manuels disponibles sur notre site Web.


Angaben zur Verarbeitung entnehmen Sie bitte der Geräteübersicht und den Betriebsanleitungen auf unserer Website.


Per informazioni sull'installazione preghiamo consultare i manuali e la panoramica degli attrezzi sul nostro sito web.

Para ver información sobre máquinas de colocación, consulte nuestra página web, apartados visión general de máquinas y manuales.

English	Français	Deutsch	Italiano	Español
Dome head	Tête plate	Flachrundkopf	Testa tonda	Cabeza alomada
Aluminium alloy* (5 % Mg)	Alliage d'aluminium* (5% Mg)	Aluminium* (5 % Mg)	Lega di alluminio* (5% Mg)	Aluminio* (5% Mg)
Natural	Brut	Blank	Nessuna finitura	Natural

*: BS 1473 5056A DIN 1725 AlMg5 Werkstoff 3.3555



ø			øA	øB	C	D		Fasteners per pod/ Nombre de rivets par chargeur/ Niete pro Magazin/ Rivetti per carica- tore / Uds./carga	Part No/ref
nom.	min.	max.	max.	max.	max.	max.	kN ¹⁾	± 1	
2.5	2.50	2.60	4.14	0.94	5.18	2.48	0.03	51	01189-02506
					6.78			41	01189-02508
					8.36			33	01189-02510
					9.96			28	01189-02512
					11.53			24	01189-02514
					13.13			21	01189-02516
					14.71			19	01189-02518
					16.31			17	01189-02520
					17.88			16	01189-02522
2.8	2.80	2.90	4.14	0.94	5.18	2.75	0.04	52	01189-02806
					6.78			41	01189-02808
					8.36			33	01189-02810
					9.96			28	01189-02812
					11.53			24	01189-02814
					13.13			21	01189-02816
					14.71			19	01189-02818
					16.31			17	01189-02820
					17.88			16	01189-02822

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

1) typical values / valeurs moyennes / typische Werte / Valori tipici / resistencias máximas recomendadas