




Dimension								
No. of Contacts	A	B	C	D	E	F	G	H
14	12.96	25.60	38.10	29.00	8.20	21.60	39.90	7.0
24	23.76	36.30	48.80	39.90	8.60	21.00	39.60	9.0
36	36.72	49.30	61.80	53.20	7.90	22.60	40.50	11.5
50	51.84	64.40	77.00	68.10	8.60	24.90	44.30	12.5

Shell
Steel

Contacts
Phosphor bronze

Insulator
PBT glass fibre reinforced
UL94 V-0

Current rating
5A

Withstanding voltage
1000V AC 1 minute

Insulation resistance
1000M Ω min. (500V DC)

Operating temperature
-55°C to +105°C

RoHS
Compliant

ITEM NO

A-57-XXM-R

TITLE

Centronics-Connectors, Male, Assembly Type

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 – Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
© Copyright 2008 by Assmann Electronic Components
All International Rights Reserved