

DESCRIPTION: #16-3 SOOW FLEXIBLE RUBBER CORD

JACKET:

COLOR: YELLOW (MUNSELL 5Y 8/12)

DIA: .385"-.430" PER UL STD. 62

THICKNESS: .060"

MATERIAL: CPE

IMPRINT: 16 AWG (1.31mm²) 3/C SOOW "SEE NOTE 5" (UL) 600V -40C TO 105C -- CSA "SEE NOTE 6" SOOW
600V -40C TO 105C FT2 WATER RESISTANT

IMPRINT COLOR: BLACK

IMPRINT TYPE STYLE: HELVETICA MEDIUM, 3/32" HIGH AND 12" REPEAT (FROM END TO BEGINING).

CONDUCTOR:

STRANDING: 26 X .010" ANNEALED BARE COPPER (26 X #30)

INSULATION DIA: .121" (ALL CONDUCTORS)

INSULATION THICKNESS: .030"

INSULATION MATERIAL: EPDM

CONSTRUCTION:

LAY LENGTH: 1.5"

FILLER: MOISTURE RESISTANT PAPER FILLERS.

RATING:

VOLTAGE: 600V

UL: LISTED SOOW 105°C (-40°C)

CSA: CERTIFIED SOOW 105°C (-40°C)

MSHA: APPROVED

PREFERRED COLOR ROTATION OF CORD
(SAME AS FACE VIEW OUR MALE DEVICES)

