

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [39533-7523](#)  
**Status:** **Active**  
**Overview:** Eurostyle™ Terminal Blocks  
**Description:** 5.08mm Pitch Eurostyle™ Vertical Plug, Rear Wire Entry, Green Housing, Gold (Au) Plated, 23 Circuits

**Documents:**

|                               |                                                          |
|-------------------------------|----------------------------------------------------------|
| <a href="#">3D Model</a>      | <a href="#">Product Specification PS-39500-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>     |

**General**

|                |                                            |
|----------------|--------------------------------------------|
| Product Family | Terminal Blocks                            |
| Series         | <a href="#">39533</a>                      |
| Application    | N/A                                        |
| Comments       | Rear Wire Entry                            |
| Component Type | Plug                                       |
| Overview       | <a href="#">Eurostyle™ Terminal Blocks</a> |
| Product Name   | ESE, Eurostyle™ Pluggable                  |
| Type           | Euro Block                                 |
| UPC            | 822350532792                               |

**Physical**

|                               |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 23                             |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | Yes                            |
| Number of Rows                | 1                              |
| Orientation                   | Vertical                       |
| Panel Mount                   | No                             |
| Pitch - Mating Interface      | 5.08mm                         |
| Pitch - Termination Interface | 5.08mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40°C to +105°C                |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm²                 | 0.13 - 3.31                    |


**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 18A  |
| Voltage - Maximum             | 300V |

**Material Info**

**Reference - Drawing Numbers**

|                       |              |
|-----------------------|--------------|
| Product Specification | PS-39500-001 |
| Sales Drawing         | SD-39533-002 |



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[39533Series](#)

**Mates With**

[39531](#) Vertical PCB Header, [39532](#)  
Horizontal PCB Header, Most 5.08mm Pitch  
Industry Standard PCB Headers, [39538](#)  
Dual Level Header, Open Ends

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39533-7523](#)