



Description: TNC crimp plug RG8X
Part No: CPMCTNC17
Application: For RG8X Cable
Crimp Tool: 24-9959P
Impedance: 50 Ohms
Frequency Range: 0-11 GHz
Material:
Body Zinc Nickel plated
Contact Brass Ni/Au plated
Insulator PTFE
Crimp sleeve Brass Nickel plated
Coupling nut Zinc Nickel plated
RoHS Compliance: Yes
Technical Detail: Refer to Emerson Document P/N 28-0000




DRAWING NO.

CPMCTNC17-CUST

REVISIONS

01	OFFICAL RELEASE									
	08-17-09	J	J	T	T					
02	RELEASE FOR SUPPLIER ALTER									
	07-27-11	Y	G	Y	G	M	L			<i>Lin</i>

CUSTOMER COPY



DIM OUTLINE

受控 CONTROLLED DOCUMENT					
编号 P/N	CPMCTNC17-CUST	版本 Rev	02	日期 Rel'd Date	Aug4,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
		YUGE HU	07-27-11
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	YUGE HU	07-27-11
X.X	± 0.2	APPROVED BY	DATE
X.XX	± 0.1	LIN MA	07-27-11
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 EMERSON Network Power		Connectivity Solutions	
TITLE TNC CRIMP PLUG RG8X			
SHEET 1 OF 1	DRAWING NO. CPMCTNC17-CUST		SIZE A