


Type 12 Modular Dust-Tight Equipment Cabinet **C3** Series

Note: This product line has been discontinued as a stocked series. Information is for reference only. For alternative solution assistance, please contact Hammond Customer Service - sales@hammfg.com or USA (716) 630-7030, Canada and International (519) 822-2960.




Looking for a deal? There are C3 products in our Clearance Section. [Click here to learn more.](#)

Features

- NEMA 12 rated - ideal for use in harsh factory floor situations.
- Oil resistant gaskets are permanently secured on all openings.
- Sides and doors (link provided below) are easily removable for easy internal access.
- Choice of two depths.
- Unit is shipped as a welded frame only with four (4) leveling feet.
- Heavy duty 14 gauge welded steel frame.
- Frame ships with reinforced lifting eyes.
- Finished in a rugged, beige textured powder paint.
- Tested to nearly double the suggested load rating of 1,500 lbs.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Side Panel Locking Kit
- Adjustable Depth 4-Post Rack Mount Shelf
- Sliding Keyboard Shelf
- Outlet Strips
- Horizontal Ring Cable Manager
- Horizontal Lacing Strip
- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Four Post Mounting Sliding Shelf
- Rack Unit Label
- Adjustable Depth Cable Manager
- Horizontal Hinged Cable Manager



- Cable Management Arm
- Vertical Cable Tray
- Rack Panels
- C2/C3 Bolt Down Kit
- Horizontal Steel Finger Cable Manager
- Mounting Hardware
- Grounding
- Climate Control

C3 Frames

Part No.	Overall Dimensions			Usable Mounting Dimensions		Rack (Pair) Units	Side Panel	Tapped 10-32	Square Hole
	Height	Width	Depth	Height	Depth		Part No.	Comination Rail Part No.	L-Panel Rail Part No.
C3F196323CG1	70.31	23.00	23.63	63.06	21.63	36U	C3SP6323CG1	CCR63TZPL	CPR63SZPL
C3F197023CG1	77.31	23.00	23.63	70.06	21.63	40U	C3SP7023CG1	CCR70TZPL	CPR70SZPL
C3F197823CG1	86.06	23.00	23.63	78.81	21.63	45U	C3SP7823CG1	CCR78TZPL	CPR78SZPL
C3F196331CG1	70.31	23.00	31.50	63.06	29.50	36U	C3SP6331CG1	CCR63TZPL	CPR63SZPL
C3F197031CG1	77.31	23.00	31.50	70.06	29.50	40U	C3SP7031CG1	CCR70TZPL	CPR70SZPL
C3F197831CG1	86.06	23.00	31.50	78.81	29.50	45U	C3SP7831CG1	CCR78TZPL	CPR78SZPL

C3 Doors

Solid Door With Handle Part No.	Solid Door With Quarter Turn Part No.	Window Door Part No.	Solid Cover Part No.	Use with Cabinet Frame	
				Rack Units	Height
C3DS1963HCG1	C3DS1963QCG1	C3DS1963PCG1	C3CS1963SCG1	36U	63.00
C3DS1970HCG1	C3DS1970QCG1	C3DS1970PCG1	C3CS1970SCG1	40U	70.00
C3DS1978HCG1	C3DS1978QCG1	C3DS1978PCG1	C3CS1978SCG1	45U	78.75

C3 Accessories

Baying Kit Beige Part No.	Bottom Plinth Black Part No.	Bottom Plinth Beige Part No.	Caster Kit Part No.	Use with Cabinet Frame		
				Rack Units	Height	Depth
C3JK6323	CPL19423BK1	CPL19423CG1	C3CRS19	36U	63.00	23.63
C3JK7023	CPL19423BK1	CPL19423CG1	C3CRS19	40U	70.00	23.63
C3JK7823	CPL19423BK1	CPL19423CG1	C3CRS19	45U	78.75	23.63
C3JK6331	CPL19431BK1	CPL19431CG1	C3CRS19	36U	63.00	31.50
C3JK7031	CPL19431BK1	CPL19431CG1	C3CRS19	40U	70.00	31.50
C3JK7831	CPL19431BK1	CPL19431CG1	C3CRS19	45U	78.75	31.50

Data subject to change without notice