




5RCC

New



Part No	Inductance (µH)	f _L (MHz)	Tol ± (%)	DCI (A)	Temp. rise Δ (°C)	ISAT (A)	DCR (Ω)	Dimensions					
								Ø d	Ø D1	(A)	Ø D	F	F1
5RCC-2R5M-00	2.5	1	20	6.0	<15	18.0	0.005	1.00	5.0	20	7.3	11.0	6.1
5RCC-4R7M-00	4.7	1	20	5.0	<15	13.0	0.008	0.95	5.0	25	7.2	14.5	6.0
5RCC-7R0M-00	7.0	1	20	3.0	<15	11.0	0.017	0.71	5.0	20	6.7	15.3	5.7
5RCC-100M-00	10.0	0.1	20	2.0	<15	9.0	0.027	0.63	5.0	20	6.5	16.2	5.7
5RCC-120M-00	12.0	0.1	20	2.5	<15	8.5	0.024	0.63	5.0	25	6.5	14.9	5.7
5RCC-250M-00	25.0	0.1	20	1.0	<15	5.0	0.038	0.63	5.0	30	6.5	22.8	5.7

Material : Ferrite

SPQ : Loose / Box 800 [-00]

All dimensions in mm

Rod Core Chokes