



120-103

Series 74 Helical Convoluted Tubing (MIL-T-81914)
 Natural or Black PFA, FEP, PTFE, Tefzel® (ETFE) or PEEK
 Type B - With External Black Dacron® Braid

MIL-T-89194 helical convoluted tubing with external black Dacron® braid

How To Order





Table I				
Dash No.	Frac. Size	Ø A Inside		Ø B Max
		Min	Max	
06	3/16	.181	.188	.430 (10.9)
09	9/32	.273	.281	.474 (12.0)
10	5/16	.306	.312	.510 (10.2)
12	3/8	.359	.375	.571 (14.5)
14	7/16	.427	.437	.631 (16.0)
16	1/2	.480	.500	.710 (18.0)
20	5/8	.603	.625	.830 (21.1)
24	3/4	.725	.750	.990 (25.1)
28	7/8	.860	.875	1.133 (28.7)
32	1	.970	1.000	1.286 (32.8)
40	1 1/4	1.205	1.250	1.599 (40.6)
48	1 1/2	1.437	1.500	1.892 (48.0)
56	1 3/4	1.688	1.750	2.192 (55.6)
64	2	1.937	2.000	2.442 (62.0)



Material and Finish

Convoluted Tubing: See Table II

Dacron Braid: Black, per Federal Specification BT 285D

Notes

Packages and spools identified with manufacturer's name and part number.

Unless otherwise specified, Conduit will be shipped per standard package minimum length supplied will be 10 feet (3M).

Consult factory for PTFE sizes not shown.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

<u>120-103-1-1-09BE</u>	<u>120-103-1-1-09BP</u>	<u>120-103-1-1-10BE</u>	<u>120-103-1-1-10CK</u>	<u>120-103-1-1-12BE</u>	<u>120-103-1-1-12BF</u>
<u>120-103-1-1-12BK</u>	<u>120-103-1-1-14BE</u>	<u>120-103-1-1-14BF</u>	<u>120-103-1-1-14BK</u>	<u>120-103-1-1-16BF</u>	<u>120-103-1-1-16BK</u>
<u>120-103-1-1-16CF</u>	<u>120-103-1-1-20BF</u>	<u>120-103-1-1-20BK</u>	<u>120-103-1-1-20CF</u>	<u>120-103-1-1-24BE</u>	<u>120-103-1-1-24BF</u>
<u>120-103-1-1-24BK</u>	<u>120-103-1-1-24CF</u>	<u>120-103-1-1-28BE</u>	<u>120-103-1-1-12CK</u>	<u>120-103-1-1-32BK</u>	<u>120-103-1-1-09BF</u>