




REV.	DATE	ECR NO.	DESCRIPTION
NC	03/20/03	—	INITIAL RELEASE
A	01/21/09	100076	REVISE BODY PLATING TO NICKEL
B	02/05/09	—	ADD NOTE 1.



NOTES:
1. VSWR 1.15 MAX @ 3GHz.

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex BNC P.C. MOUNT RECEPTACLE JACK (75 ohm)									
8					DRAWN	GRS	02/05/09											
7					CHECKED													
6					ISSUED				PART DESCRIPTION									
5					SHEET	1 OF 1												
4								PART NO.										
3	CONTACT PIN	PHOS. BRONZE	GOLD	1														
2	INSULATOR	PTFE	NATURAL	1				112515-75										
1	BODY	BRASS	NICKEL	1														
DESCRIPTION				MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE		DWG. NO.	112515-75.DWG	REV.	B	SIZE	A	SCALE	NA
							C:/112/112515-75.DWG											