


PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA18-A THRU PCA18-Z	'A' THRU 'Z'	30	300	1	10	.185" - .234"
PCA18-A-J	'A' - 'J' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-K-T	'K' - 'T' [1 EA.]	30	300	1	10	.185" - .234"
4 PCA18-U-Z	'U' - 'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.185" - .234"
PCA18-0 THRU PCA18-9	'0' THRU '9'	30	300	1	10	.185" - .234"
4 PCA18-0-9	'0' - '9' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-MIN	' - '	30	300	1	10	.185" - .234"
PCA18-PLS	' + '	30	300	1	10	.185" - .234"

NOTES:

1. COLOR: WHITE WITH BLACK LEGENDS.
2. MILLIMETERS ARE IN [].



SYMBOLS ARE LOCATED ON BOTH SIDE OF MARKERS.

CAD FILENAME/LAYERS 100281DC-DC-C10396/04D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PCA18-* CLIP-ON WIRE MARKER

3	3/28/11	RVU		ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336	R					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .062 (.XXX) ± .015 (.XX) ± .031 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079	R							
1	10-06-06	RVU		ADDED TOLERANCE AND REVISED TABLE.	4881	R				DRAWN BY RVU	MAT'L: WHITE MARKER -ACETAL	SCALE	
0	9-12-06	RVU		DRAWING RELEASE	3732	R				DATE 10-14-04		DRAWING NO. C10396	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCA18-1](#) [PCA18-2](#) [PCA18-3](#) [PCA18-4](#) [PCA18-5](#) [PCA18-6](#) [PCA18-7](#) [PCA18-8](#)