




REV.	DATE	DESCRIPTION
NC	09/23/99	INITIAL RELEASE
A	11/22/05	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
6					0.5 - 8mm ± 0.20mm
5					8 - 30mm ± 0.40mm
4	GASKET	SILICONE	RED	1	30 - 120mm ± 0.50mm
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
2	INSULATOR	TEFLON	NATURAL	1	.020 - .315 = ± 0.007"
1	BODY	BRASS	NICKEL	1	.315 - 1.180 = ± 0.015"
					1.180 - 4.724 = ± 0.020"
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING
					CAD FILE C:/122/122443.DWG
					DWG. NO. 122443.DWG
					REV. A
					SIZE A
					SCALE NA
					PART NO. 122443
					PART DESCRIPTION TNC PANEL JACK - EXTENDED TEFLON
					SHEET 1 OF 1
					CHECKED
					DRAWN G.R.S.
					DATE 11/22/05
					APPROVALS

Amphenol Connex

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122443](#)