





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7683SBP	5.0	.060	.050	0.63	100,000	C-2R
7715SBP	5.0	.115	.150	1.89	40,000	C-2R
8097SBP	12.0	.060	.150	1.89	16,000	C-2F
CB48SBP	14.0	.040	.150	1.89	16,000	C-2F
8098SBP	14.0	.065	.150	1.89	16,000	C-2F
8099SBP	18.0	.026	.150	1.89	16,000	C-2F
7839SBP	28.0	.024	.150	1.89	16,000	CC-2F

*LAMP RATED ONLY (NOT IN BASE)

NOTES:

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: NYLON OR EQUIVALENT.
3. BASE COLOR: WHITE.
4. PIN MATERIAL: NICKEL WIRE, GOLD PLATED.
5. LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
6. FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
7. DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.



DIMENSIONS ARE IN MILLIMETERS
TOLERANCE UNLESS OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/- 0
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 SPECIAL BI-PIN BASED LAMPS

REV. NO.

ADD CB48SBP-CANCEL DRAW. CB48SBP/K & CB48SBP/S

4/17/00

DRAWN BY

L. WENGSTROM

APP'D BY DATE

BW 4/17/00

SIZE

A

FSCM NO.

55335

DRAWING NO.

BI-PIN T-1 SPECIAL

SCALE

NONE

RELEASED DATE

3/15/00

REVISION DATE

4/17/00

REV. NO.

A

SHEET 1 OF 1

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

DESCRIPTION/ECO NUMBER

APP'D DATE