

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: Nylon-6T, UL 94V-0

Contact Plating: Flash Gold

Contact Material: Brass


Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.


Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



NUMBER OF POSITIONS	DIMENSIONS		
	A	B	C
10	5.08	11.25	12.65
14	7.62	13.79	15.19
16	8.89	15.06	16.46
20	11.43	17.60	19.00
26	15.24	21.41	22.81
30	17.78	23.95	25.35
34	20.32	26.49	27.89
40	24.13	30.30	31.70
50	30.48	36.65	38.05
60	36.83	43.00	44.40



Recommended PCB Layout

UNLESS TOLERANCE		DRAW BY	
GENERAL	ANGLE	DESIGN BY	
X. ± 0.30	X.° ± 3.0°	CHECK BY	
.X. ± 0.25	.X.° ± 2.0°	APPROVE BY	
.XX ± 0.20	.XX.° ± 1.0°		
.XXX ± 0.10	.XXX ± 0.5°		
SCALE	SHEET	UNIT	Port NO.
1:1	1/1	MM	3220-XX-0200-00
DRAW NO:			REV: A

CnC Tech,LLC

3220-XX-0200-00