



For Utility Metering Applications

(Typical values @+ 25°C for batteries stored for one year or less)

- | | | |
|---|--|------------------|
| ■ | Nominal capacity @ 3 mA, to 2 V | 8.5 Ah |
| ■ | Rated voltage | 3.6 V |
| ■ | Maximum recommended continuous current | 230 mA |
| ■ | Maximum pulse current capability | 400 mA |
| ■ | Weight | 55 g (1.94 oz) |
| ■ | Operating temperature range | -55 °C to +85 °C |
| ■ | Li metal content | approx. 2.5 g |
| ■ | U.L. Component Recognition, MH 12193 | |



Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.