




NOTE: End Cap to be impression stamped with "JKL and applicable PART NUMBER."

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
GF540	6.0	.100	.10	1.26	10,000	C-8
GF550	6.0	.200	.40	5.03	5,000	C-8
GF570	6.3	.250	.64	8.04	10,000	C-8
GF560	6.3	.300	.64	8.04	10,000	C-8
GF660	8.0	.150	.40	5.03	10,000	C-8
GF665	8.0	.200	.25	3.14	10,000	C-8
GF670	8.0	.250	.64	8.04	10,000	C-8
GF680	8.0	.300	.90	11.31	10,000	C-8
GF710	12.0	.100	.23	2.89	10,000	C-8
GF780	12.0	.150	.70	9.00	5,000	C-8
GF740	12.6	.300	.64	8.04	5,000	C-8



METRIC
DIMENSIONS ARE IN MILLIMETERS
TOLERANCE UNLESS OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/-

JKL COMPONENTS CORPORATION

TITLE

T-2 FUSE STYLE (3AG) LAMPS

DRAWN BY
L. WENGSTROM

APPVD BY DATE
ED 3/1/01

SIZE
A

PSCM NO.
55335

DRAWING NO.

FUSE GF SERIES T-2

- CAD DRAWING -

SCALE

NONE

RELEASED DATE 3/1/01

REVISION DATE

REV. NO.

SHEET 1 OF 1

REV. NO. DESCRIPTION/ECO NUMBER

3/1/01 APPVD DATE

MANUAL REVISIONS NOT PERMITTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[GF780](#) [GF550](#) [GF540](#) [GF570](#) [GF660](#) [GF665](#) [GF670](#) [GF680](#) [GF710](#) [GF740](#) [GF560](#)