


REV.	DATE	DESCRIPTION
NC	06/07/00	INITIAL RELEASE
A	05/24/07	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.							05/24/07
7						CHECKED			PART DESCRIPTION UHF FEMALE TO FEMALE THREADED ADAPTER					
6						ISSUED								
5						SHEET	1 OF 1		PART NO. 182319					
4	HEX NUT	BRASS	NICKEL	2	CAD FILE			DWG. NO. 182319.DWG REV. A SIZE A SCALE NA						
3	CONTACT PIN	BRASS	GOLD	1	C:/182/182319.DWG									
2	INSULATOR	DELIN	NATURAL	1	DO NOT SCALE DRAWING									
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY										