


REV.	DATE	ECR NO.	DESCRIPTION
NC	03/25/08	—	INITIAL RELEASE
A	11/22/08	—	REVISE BODY CONFIGURATION



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex													
8					DRAWN	GRS	11/22/08															
7					CHECKED																	
6									PART DESCRIPTION													
5									SMA R/P JACK TO R/P JACK													
4									PART NO.													
3	CONTACT PIN	BRASS	GOLD		1				132169RP-RP													
2	INSULATOR	PTFE	NATURAL	1				DWG. NO.														
1	HOUSING/BODY	BRASS	GOLD	1				CAD FILE		C:/132/132169RP-RP.DWG		DWG. NO.		132169RP-RP.DWG		REV.	A	SIZE	A	SCALE	NA	
DESCRIPTION				MATERIAL	FINISH	QTY																