


NOTES: UNLESS OTHERWISE SPECIFIED

- 1. P/N: 9205-HS
INSULATOR: HEAT SHRINK TUBING 221. BLACK.
BODY: BRASS. 40μ [1.02μm] MIN GOLD OVER NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. 40μ [1.02μm] MIN GOLD OVER NICKEL PLATED.

- 2. P/N: 9202COLOR
HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

- 3. P/N: W-200/COLOR
22AWG 65X40 TINNED COPPER
0.070 [1.78] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

- 4. PERFORMANCE
MAXIMUM CURRENT: 2.5 AMPS
MAXIMUM VOLTAGE: 1000 (300 UL) W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± ±		CONTRACT NO.		APPROVALS		DATE		DESCRIPTION	
		MATERIAL SEE NOTE.		DRAWN R.L.		APPROVED BY				0.025 [0.64] SQ. SOCKET TO STD BAN PLUG (9202)	
		FINISH SEE NOTE.								SIZE CODE IDENT NO. DRAWING NO.	
		NEXT ASSY USED ON								A 08505 9166	
		APPLICATION		DO NOT SCALE DRAWING						SCALE 1:1	
										SHEET 1 OF 1	

E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.