

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0877057010

Status:

Active - Custom

Description:

1.00mm (.039") Pitch DDR-II DIMM 240 Circuits Socket, Vertical, 1.8 Voltage, 2.54mm (.100") Tail Length, White Latches, Nylon 6/6 Glass-filled, White Housing, Gold (Au) Flash, Beveled Metal Pins Width 2.70mm (.106"), Lead Free

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Memory Module Sockets
Series	87705
Comments	White Latches Insertion Force: 10Kg (98N) Max. Beveled Metal Pin Width: 2.70mm (.106")
Component Type	Socket
JEDEC Outline	MO-237
Product Name	DDR2 DIMM
Physical	
Circuits (Loaded)	240
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
Material - Plating Mating	Gold
PC Tail Length	2.54mm (.100")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	1.00mm (.039")
Temperature Range - Operating	-10°C to +85°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	30V
Voltage Key	1.8V, Center
Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)
Process Temperature max. C	260
Material Info	

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87705Series

Mates With

JEDEC standard 1.27mm modules

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION