



## SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	12	Vdc
OPERATING VOLTAGE RANGE	3 ~ 28	Vdc
RATED CURRENT (MAX)	8	mA
MINIMUM SPL @ 10 CM	95	dBA
RESONANT FREQUENCY	2,500 ± 500	Hz
TONE OR PULSE RATE	CONTINUOUS	0 pulse /sec
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +80	°C
HOUSING MATERIAL	ABS	-
TERMINAL MATERIAL	LEAD WIRE	-
WEIGHT	6.8	grams

THIS DOCUMENT CONTAINS DATA  
PROPRIETARY TO PROJECTS UNLIMITED, INC.  
ANY USE OR REPRODUCTION, IN ANY FORM,  
WITHOUT PRIOR WRITTEN PERMISSION OF  
PROJECTS UNLIMITED, INC. IS PROHIBITED.  
©2003, Projects Unlimited Inc.

## REVISION HISTORY

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	9/08/2006	
A	REVISED MINIMUM SPL	8/02/2007	D.F.
B	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	2/11/2008	B.R.



## NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE  
SPECIFIED:  
DIMENSIONS ARE IN  
MILLIMETERS,  
TOLERANCES  
ARE ±0.5 AND  
ANGLES ARE ±3°.  
AI-3025-TF-LW80-R.idw

SIZE  
A3

Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date
J.D.	9/8/2006	R.W.	9/8/2006	B.R.	9/8/2006	2/11/2008

 pui  
audio™  
INC  
a projects unlimited company

AI-3025-TF-LW80-R

Indicator

Edition  
-  
Sheet  
1 / 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-3025-TF-LW80-R](#)