



LEAD-FREE P/N	CABLES	ød1	ød2	ød3	ød4	d5	d6	Remarks
70297-001LF	RG 178B/U, RG196A/U TZX_50126	1.10	1.70	2.20	3.20	7.8	21.00	
70297-002LF	RG188A/U, RG174A/U, RG316/U	1.70	2.50	2.90	3.60	9.0	22.20	
70297-004LF	TZX_75106 (GORE CABLE) 75ohm	1.30	2.00	2.50	3.20	7.8	21.00	see note 2
70297-005LF	RG 179 75ohm	1.70	2.50	2.90	3.60	9.0	22.20	see note 2
70297-006LF	FILOTEX CABLE ALCATEL	1.30	2.00	2.50	3.20	7.8	21.00	see note 2




1.27µm Au Min.
Positions 1&2
Plating on contact area

NOTES:

- All dimensions shown are references.
- When used with 75 ohm cables the performance of the contact will be lower.
- Pull out force of center contact must be 0.1 N min. / 0.8 N max.
- This product will be packed in a small plastic bag containing three loose parts, as follows.
 - Crimp Ferrule
 - Outer Contact
 - Inner Contact
- Assemble product with tool HT430, use inserts EPL 193460 or EPL 193428.
- THIS PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS -22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
- PACKAGING SPEC: SEE GS-14-920

rev	ecn no	dr	date
J	LS06-0022	LGO	2006/03/04
K	LS07-0214	LGO	2007/08/20
L	LS07-0249	LGO	2007/10/02
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	GOISNARD	2006/03/04	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5		
Eng	GOISNARD	2006/03/04			0.XX	±0.1				
Chr	LEGARE	2006/03/04			0.XXX	±0.1				
Appr	LEGARE	2006/03/04	Product family				METRAL		Spec ref -	
			title CRIMP TO CABLE RECEPTACLE MINI COAX				dwg no 70297		Rev.	
									L	
catalog no			-				CUSTOMER		sheet 1 of 1	



CRIMP TO CABLE
RECEPTACLE MINI COAX

70297

CUSTOMER sheet 1 of 1