





Neutral disconnect terminals

WNT 2.5

WNT 4

WNT 6

WNT 10



Max. technical data

Dimensions / approvals

Width/length/height (mm) with TS 35 x 7.5

Insulation stripping length/clamping screw/screwdriver blade

VDE rated data 0611 Part 5

Rated voltage/current/cross-section

Rated voltage/impulse voltage/pollution severity

Further technical data

Tightening torque range clamping screw / N disconnect Nm

Torque setting with DMS 2 electric screwdriver

Clampable conductors

Solid H07V-U mm²

Stranded H07V-R mm²

Flexible H07V-K mm²

Flexible H07V-K and ferrule acc. to DIN 46 228/1 mm²

Flexible H07V-K and ferrules with plastic insul. collar mm²

Max. clamping range in mm²/Gauge pin acc. to 60 947-7-1 Size

Cont. current of cross-connect. 2-pole A

Cont. current of cross-connect. multi-pole A

UL/CSA rated data

Voltage/current/conductor size UL

Voltage/current/conductor size CSA

Ordering data

Version

For busbar 10 x 3 Blue Wemid

For busbar 10 x 3 as PA disconnect Dark beige Wemid

(VDE 0107)

32 A/4 mm²

5/60/47

10 mm/M 2.5/3.5 x 0.6

400 V/24 A/2.5 mm²

400 V/6 kV/3

0.4...0.6 / 0.4...0.6

1

0.5...4

1.5...4

0.5...4

0.5...2.5

0.5...2.5¹⁾

0.13...4 A 3

600 V/25 A/22...12 AWG

600 V/20 A/26...12 AWG

Type Cat. No. Qty.

WNT 2.5 1010680000 100

WNT 2.5 1010600000 100

41 A/6 mm²

6/60/47

10 mm/M 3/3.5 x 0.6

400 V/32 A/4 mm²

400 V/6 kV/3

0.5...1.0 / 0.4...0.8

2

0.5...6

1.5...6

0.5...6

0.5...4

0.5...4

0.13...6 A 4

600 V/35 A/22...10 AWG

600 V/35 A/26...10 AWG

Type Cat. No. Qty.

WNT 4 1010780000 100

WNT 4 1010700000 100

57 A/10 mm²

8/60/47

12 mm/M 3.5/4.0 x 0.8

400 V/41 A/6 mm²

400 V/6 kV/3

0.8...1.2 / 0.8...1.6

3

0.5...10

1.5...10

0.5...10

0.5...6

0.5...6

0.5...10 A 5

600 V/45 A/20...8 AWG

600 V/45 A/20...8 AWG

Type Cat. No. Qty.

WNT 6 1010880000 50

WNT 6 1010800000 50

76A/16 mm²

10/60/47

12 mm/M 4/5.5 x 1.0

400 V/57 A/10 mm²

400 V/6 kV/3

1.2...2.0 / 0.8...1.6

4

1.5...16

1.5...16 (16 mm² w. 2.4 Nm)

1.5...16

1.5...16

1.5...16

1.31...16 B 6

600 V/60 A/16...8 AWG

600 V/65 A/16...6 AWG

Type Cat. No. Qty.

WNT 10 1010980000 50

WNT 10 1010900000 50

