




NOTES:

1. MATERIAL:

1.1 HOUSING:

10089717-XXXXX0LF: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR: NATURAL.

10089717-XXXXX1LF: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR: BLACK.

1.2 COVER: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR:NATURAL.

1.3 CONTACT: BRASS ALLOY.

2. FINISH:

UNDER PLATING: 50u" MIN. NICKEL OVERALL

CONTACT AREA AND SOLDER TAIL: MATTE TIN 100u" MIN. OVERALL

3. REFLOW SOLDER CAPABLE TO 260°C PEAK TEMP. FOR 10 SECONDS MAX.

4. SPEC. PLS. REFER TO GS-12-574.

5. PACKAGE PLS. REFER TO GS-14-1316.

6. PART NUMBER DESCRIPTION:

10089717-XXX X X X LF
 NO. OF CONTACTS
 PACKING
 0: TAPE & REEL WITH COVER
 LEAD FREE
 COLOR
 0: NATURAL
 1: BLACK
 PLATING
 0: MATTE TIN

CKT	Dim.A	Dim.B
007	9.0	11.8

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.25			projection 	title 1.5mm WIRE TO BOARD HEADER SMT VERTICAL TYPE		
A	T08-1164	WL	08/11/08		.XX ± 0.15						
B	T08-1185	WL	11/13/08		.XXX ± 0.10						
C	T08-1196	WL	12/10/08	angles	0° ± 2°				product family WIRE TO BOARD size dwg no A4 10089717		
D	T09-1005	WL	01/20/09	dr	LEIF SHEN	06/18/08	scale				
E	T09-1146	WL	11/16/09	enrg	LEIF SHEN	06/18/08					
				chr	LEIF SHEN	06/18/08					
				appd	JOSEPH HSIA	06/18/08					
sheet index	revision sheet	E 1									