

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301060112](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets, NEMA 5-15 Plug, Overall Length 15.24m (50.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Super-Safeway
Type	String Lights
UPC	78678879893
Physical	
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	107.95mm (4.250")
Length	15.24m (50.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	6014.634/g
Packaging Type	Carton
Socket Construction	Rubber Molded

Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info	
Engineering Number	323523



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130106](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION