







THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION	
CHARACTERISTICS			SCALE FULL	
OPERATING FORCE----- 6-12 LB			DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE----- 30 LB MAX			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE----- 4 LB MIN			ONE PLACE (.0) ±.030	
PRETRAVEL----- .040 MAX			TWO PLACE (.00) ±.015	
DIFFERENTIAL TRAVEL----- .020 MAX			THREE PLACE (.000) ±.005	
OVERTRAVEL----- .250 MIN			ANGLES ±	
			WEIGHT	
ELECTRICAL DATA				
		CONTACT ARRANGEMENT 2X SPDT 6		
LOAD	28 VDC			
	SEA LEVEL	50,000 FT.		
RES	1.0			
IND	0.5			

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 6 - GOLD CONTACT BASIC SWITCHES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN416-R4](#)