

Twist drills DIN 1897 type N HSS Co 5 ground, with split point - short

Point cut: helical point
from Ø 3,0 mm
with split point DIN 1412 C

Point angle: 135°
Helix angle: 20-30°
Ø tolerance: h8
Surface: golden brown
Right-hand cutting

Short and stable standard drill consisting of cobalt alloyed heavy-duty high-speed steel with higher heat-resistance. Ideally suitable for assembly work in thin-walled materials such as sheet steels, flat steels and profile steels. High security against fracture. For use in all hand-held drilling machines.

Applications: for steel and alloyed cast steel over 900 N/mm² strength, grey cast, malleable cast, high-alloyed chromium steel such as stainless and acid resistant steel.

Packing unit:

Ø 2,00 mm up to 10,20 mm in plastic box of 10
Ø 10,50 mm up to 13,00 mm in plastic box of 5

[illegible][illegible]