



DESCRIPTION: 2MM SHUNT LOW PROFILE, .075" TIN/LEAD



MATERIAL: HOUSING: GLASS FILLED THERMOPLASTIC, UL 94V-0, BLACK
CONTACT: HIGH PERFORMANCE COPPER ALLOY
PLATING: TIN/LEAD ALL OVER
ELECTRICALS: CURRENT RATING: 1.0 AMPERE MAX.
CONTACT RESISTANCE: 30 MILLIOHM MAX.
DMV: 500 Vrms MIN.
INSULATION RESISTANCE: 1 X 10⁴ MOHMS
OPERATING TEMP: -55°C TO 105°C



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN: PAM JENKINS		DATE: 12-13-01	
CHECKED:		DATE:	
SCALE:	SHEET 1	OF 1	REV 1
DWG NO. 800-002-LP1-006			