







DESCRIPTION: 2MM RECEPTACLES

MATERIAL:
HOUSING: GLASS FILLED
THERMOPLASTIC UL 94V-0
COLOR: BLACK
CONTACT: PHOSPHOR BRONZE ALLOY 521
RoHS COMPLIANT

ELECTRICAL:
CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 2 mΩ MAX.
DWV: 1000 V_{rms}/MIN.
OPERATING TEMP:
-55°C TO +125°C

"L" = NO. OF CONTACTS PER ROW X .079



SERIES 206X - XX-01RPX
2063 = SINGLE ROW
2064 = DUAL ROW
POSITIONS
SINGLE - INCREMENTS OF 1
DUAL = INCREMENTS OF 2
TYPE:
01 = STRAIGHT
PLATING:
P2 = 15 u" GOLD MATING AREA,
100U" MIN. MATTE TIN ON TAILS

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS		DATE: 7-28-05	
			CHECKED:		DATE:	
	NorComp		SCALE:	SHEET 1 OF 1	REV 1	
		DWG NO. 206X-XX-01RPX				